

| ID<br>(in) | OD<br>(in) | Description  | PBC Linear | MCGILL         | CARTER       |
|------------|------------|--|------------|----------------|--------------|
| 0.126      | 0.432      | Yoke Roller Standard                                 | 6300060    |                |              |
| 0.198      | 0.558      | Yoke Roller Standard                                 | 6300061    |                |              |
| 0.125      | 0.500      | Roller Follower Concentric Studded - Steel           | 6300062    | CF 1/2 SB      | CNB-16-SB    |
| 0.125      | 0.500      | Roller Follower Eccentric Studded - Steel            | 6300063    | CFE 1/2 SB     | CNBE-16-SB   |
| 0.198      | 0.667      | Yoke Roller Standard                                 | 6300064    |                |              |
| 0.125      | 0.625      | Roller Follower Concentric Studded - Steel           | 6300065    | CF 5/8 SB      | CNB-20-SB    |
| 0.125      | 0.625      | Roller Follower Eccentric Studded - Steel            | 6300066    | CFE 5/8 SB     | CNBE-20-SB   |
| 0.250      | 0.850      | Yoke Roller Standard                                 | 6300067    |                |              |
| 0.250      | 0.875      | Yoke Roller Sealed - Grooved                         | 6300068    |                |              |
| 0.313      | 1.100      | Yoke Roller Sealed                                   | 6300069    |                |              |
| 0.625      | 2.000      | Yoke Roller Sealed                                   | 6300070    | CYR 2 S        | YNB-64-S     |
| 0.250      | 0.875      | Yoke Roller Sealed                                   | 6300071    | CYR 7/8 S      | YNB-28-S     |
| 0.312      | 1.125      | Yoke Roller Sealed                                   | 6300072    | CYR 1 1/8 S    | YNB-36-S     |
| 0.500      | 1.750      | Yoke Roller Sealed                                   | 6300073    | CYR 1 3/4 S    | YNB-56-S     |
| 0.126      | 0.432      | Yoke Roller Chrome Plated                            | 6300074    |                |              |
| 0.126      | 0.432      | Yoke Roller High Temp                                | 6300075    |                |              |
| 0.198      | 0.558      | Yoke Roller Chrome Plated                            | 6300076    |                |              |
| 0.198      | 0.558      | Yoke Roller High Temp                                | 6300077    |                |              |
| 0.125      | 0.500      | Roller Follower Concentric Studded - Stainless Steel | 6300078    | CF 1/2 SB CR   | SC-16-SB     |
| 0.125      | 0.500      | Roller Follower Concentric Studded - High Temp       | 6300079    |                | CNB-16-BHT   |
| 0.125      | 0.500      | Roller Follower Eccentric Studded - Chrome Plated    | 6300080    |                |              |
| 0.125      | 0.500      | Roller Follower Eccentric Studded - High Temp        | 6300081    |                | CNBE-16-BHT  |
| 0.198      | 0.667      | Yoke Roller Chrome Plated                            | 6300082    |                |              |
| 0.198      | 0.667      | Yoke Roller Stainless Steel                          | 6300083    |                |              |
| 0.125      | 0.625      | Roller Follower Contentric Studded- Chrome Plated    | 6300084    |                | CNB-20-SBC   |
| 0.125      | 0.625      | Roller Follower Concentric Studded - Stainless Steel | 6300085    | CF 5/8 SB CR   | SC-20-SB     |
| 0.125      | 0.625      | Roller Follower Eccentric Studded - Chrome Plated    | 6300086    |                |              |
| 0.250      | 0.850      | Yoke Roller Chrome Plated                            | 6300087    |                |              |
| 0.250      | 0.850      | Yoke Roller Chrome Plated                            | 6300088    |                |              |
| 0.250      | 0.875      | Yoke Roller Stainless Steel - Grooved                | 6300089    |                | SY-28-S      |
| 0.312      | 1.000      | Yoke Roller Chrome Plated - Sealed                   | 6300090    |                |              |
| 0.250      | 0.875      | Yoke Roller Chrome Plated - Sealed                   | 6300091    |                |              |
| 0.250      | 0.875      | Yoke Roller Stainless Steel - Sealed                 | 6300092    | CYR 7/8 S CR   | SY-28-S      |
| 0.125      | 0.625      | Roller Follower Eccentric Studded - Stainless Steel  | 6300093    | CFE 5/8 SB CR  | SCE-20-SB    |
| 0.312      | 1.125      | Yoke Roller Chrome Plated - Sealed                   | 6300094    |                |              |
| 0.250      | 1.125      | Roller Follower Eccentric Studded - Steel            | 6300096    | CFE 1 1/8 SB   | CNBE-36-SB   |
| 0.188      | 0.875      | Roller Follower Eccentric Studded - Steel            | 6300097    | CFE 7/8 SB     | CNBE-28-SB   |
| 0.750      | 2.500      | Yoke Roller Sealed                                   | 6300098    | CYR 2 1/2 S    | YNB-80-S     |
| 0.312      | 1.000      | Yoke Roller High Temp - Sealed                       | 6300118    |                | YNB-32-S-BHT |
| 0.312      | 1.125      | Yoke Roller High Temp - Sealed                       | 6300119    |                | YNB-36-S-BHT |
| 0.312      | 1.000      | Yoke Roller Stainless Steel - Sealed                 | 6300122    | CYR 1 S CR     | SY-32-S      |
| 0.312      | 1.125      | Yoke Roller Stainless Steel - Sealed                 | 6300123    | CYR 1 1/8 S CR | SY-36-S      |