



Ball Bearing Slew Rings

ID (mm)	OD (mm)	Description	PBC Linear	KAYDON
50	110	Steel Rings	SRB-BMT-0050-0110-STNN	MTO-050
50	110	Steel Rings with Threaded Holes	SRB-BMT-0050-0110-STNT	MTO-050T
65	135	Steel Rings	SRB-BMT-0065-0135-STNN	MTO-065
65	135	Steel Rings with Threaded Holes	SRB-BMT-0065-0135-STNT	MTO-065T
122	226	Steel Rings	SRB-BMT-0122-0226-STNN	MTO-122
122	226	Steel Rings with Threaded Holes	SRB-BMT-0122-0226-STNT	MTO-122T
143	246	Steel Rings	SRB-BMT-0143-0249-STNN	MTO-143
143	246	Steel Rings with Threaded Holes	SRB-BMT-0143-0249-STNT	MTO-143T
145	300	Steel Rings	SRB-BMT-0145-0300-STNN	MTO-145
145	300	Steel Rings with Threaded Holes	SRB-BMT-0145-0300-STNT	MTO-145T
145	312	Steel Rings with Additional Load Capacity	SRB-BMT-0145-0312-STNL	MTO-145X
170	310	Steel Rings	SRB-BMT-0170-0310-STNN	MTO-170
170	310	Steel Rings with Threaded Holes	SRB-BMT-0170-0310-STNT	MTO-170T

Polymer Slew Rings

ID (mm)	OD (mm)	Description	PBC Linear	IGUS
20	80	Aluminum Outer Ring & Polymer Inner Ring	SRB-P02-0020-0080-ALNN-M1	PRT-02-20-AL-PLASTIC
30	100	Aluminum Outer Ring & Polymer Inner Ring	SRB-P02-0030-0100-ALNN-M1	PRT-02-30-AL-PLASTIC
50	150	Aluminum Outer Ring & Polymer Inner Ring	SRB-P02-0050-0150-ALNN-M1	PRT-02-40-AL-PLASTIC
60	160	Aluminum Outer Ring & Polymer Inner Ring	SRB-P02-0060-0160-ALNN-M1	PRT-02-50-AL-PLASTIC
100	185	Aluminum Rings	SRB-P03-0100-0185-ALNN-E1	PRT-01-100
150	250	Aluminum Rings	SRB-P03-0150-0250-ALNN-E1	PRT-01-150
200	300	Aluminum Rings	SRB-P03-0200-0300-ALNN-E1	PRT-01-200
20	80	Aluminum Rings	SRB-P03-0020-0080-ALNN-E1	PRT-01-20
30	100	Aluminum Rings	SRB-P03-0030-0100-ALNN-E1	PRT-01-30
50	150	Aluminum Rings	SRB-P03-0050-0150-ALNN-E1	PRT-01-50
60	160	Aluminum Rings	SRB-P03-0060-0160-ALNN-E1	PRT-01-60
100	185	Aluminum Rings & High Temp Sliding Pad	SRB-P03-0100-0185-ALNN-E2	PRT-01-100-H1
150	250	Aluminum Rings & High Temp Sliding Pad	SRB-P03-0150-0250-ALNN-E2	PRT-01-150-H1
200	300	Aluminum Rings & High Temp Sliding Pad	SRB-P03-0200-0300-ALNN-E2	PRT-01-200-H1
20	80	Aluminum Rings & High Temp Sliding Pad	SRB-P03-0020-0080-ALNN-E2	PRT-01-20-H1
30	100	Aluminum Rings & High Temp Sliding Pad	SRB-P03-0030-0100-ALNN-E2	PRT-01-30-H1
50	150	Aluminum Rings & High Temp Sliding Pad	SRB-P03-0050-0150-ALNN-E2	PRT-01-50-H1
60	160	Aluminum Rings & High Temp Sliding Pad	SRB-P03-0060-0160-ALNN-E2	PRT-01-60-H1
100	185	Aluminum Rings & FDA Sliding Pad	SRB-P03-0100-0185-ALNN-E6	PRT-01-100-A180
150	250	Aluminum Rings & FDA Sliding Pad	SRB-P03-0150-0250-ALNN-E6	PRT-01-150-A180
200	300	Aluminum Rings & FDA Sliding Pad	SRB-P03-0200-0300-ALNN-E6	PRT-01-200-A180
20	80	Aluminum Rings & FDA Sliding Pad	SRB-P03-0020-0080-ALNN-E6	PRT-01-20-A180
30	100	Aluminum Rings & FDA Sliding Pad	SRB-P03-0030-0100-ALNN-E6	PRT-01-30-A180

**PBC Linear**

Slew Ring Bearing Interchange Charts

Polymer Slew Rings

ID (mm)	OD (mm)	Description	PBC Linear	IGUS
50	150	Aluminum Rings & FDA Sliding Pad	SRB-P03-0050-0150-ALNN-E6	PRT-01-50-A180
60	160	Aluminum Rings & FDA Sliding Pad	SRB-P03-0060-0160-ALNN-E6	PRT-01-60-A180
100	185	Stainless Steel Rings	SRB-P03-0100-0185-SSNN-E1	PRT-01-100-ES
150	250	Stainless Steel Rings	SRB-P03-0150-0250-SSNN-E1	PRT-01-150-ES
200	300	Stainless Steel Rings	SRB-P03-0200-0300-SSNN-E1	PRT-01-200-ES
20	80	Stainless Steel Rings	SRB-P03-0020-0080-SSNN-E1	PRT-01-20-ES
30	100	Stainless Steel Rings	SRB-P03-0030-0100-SSNN-E1	PRT-01-30-ES
50	150	Stainless Steel Rings	SRB-P03-0050-0150-SSNN-E1	PRT-01-50-ES
60	160	Stainless Steel Rings	SRB-P03-0060-0160-SSNN-E1	PRT-01-60-ES
100	185	Stainless Steel Rings & ESD Sliding Pad	SRB-P03-0100-0185-SSNN-M9	PRT-01-100-ES-F2
150	250	Stainless Steel Rings & ESD Sliding Pad	SRB-P03-0150-0250-SSNN-M9	PRT-01-150-ES-F2
200	300	Stainless Steel Rings & ESD Sliding Pad	SRB-P03-0200-0300-SSNN-M9	PRT-01-200-ES-F2
20	80	Stainless Steel Rings & ESD Sliding Pad	SRB-P03-0020-0080-SSNN-M9	PRT-01-20-ES-F2
30	100	Stainless Steel Rings & ESD Sliding Pad	SRB-P03-0030-0100-SSNN-M9	PRT-01-30-ES-F2
50	150	Stainless Steel Rings & ESD Sliding Pad	SRB-P03-0050-0150-SSNN-M9	PRT-01-50-ES-F2
60	160	Stainless Steel Rings & ESD Sliding Pad	SRB-P03-0060-0160-SSNN-M9	PRT-01-60-ES-F2
100	187	Aluminum Rings & HTD8M Toothed Belt	SRB-P03-0100-0187-ALEN-E1-HTD8	PRT-01-100-TO-HTD8M
150	253	Aluminum Rings & HTD8M Toothed Belt	SRB-P03-0150-0253-ALEN-E1-HTD8	PRT-01-150-TO-HTD8M
200	304	Aluminum Rings & HTD8M Toothed Belt	SRB-P03-0200-0304-ALEN-E1-HTD8	PRT-01-200-TO-HTD8M
20	81	Aluminum Rings & HTD5M Toothed Belt	SRB-P03-0020-0081-ALEN-E1-HTD5	PRT-01-20-TO-HTD5M
30	111	Aluminum Rings & HTD8M Toothed Belt	SRB-P03-0030-0111-ALEN-E1-HTD8	PRT-01-30-TO-HTD8M
50	162	Aluminum Rings & HTD8M Toothed Belt	SRB-P03-0050-0162-ALEN-E1-HTD8	PRT-01-50-TO-HTD8M
60	167	Aluminum Rings & HTD8M Toothed Belt	SRB-P03-0060-0167-ALEN-E1-HTD8	PRT-01-60-TO-HTD8M